⊘AdvantaSil[™]

High Pressure Unreinforced Silicone Tubing

Translucent; Platinum Cured



dvantaSil High Pressure silicone tubing is a high quality, cost effective solution designed for increased flow rates to reduce your processing time. The tubing's unreinforced characteristic allows for limited pumpability up to 30 psi back pressure and makes it easier to see your process fluids. AdvantaSil High Pressure is the optimal choice for Single-Use applications such as TFF, virus filtration, inline integrity testing of filtration assemblies, and high volume fluid transfer.

AdvantaSil High Pressure tubing has undergone extensive physical, chemical and biological testing and meets USP Class VI, FDA CFR 177.2600, ISO 10993, European Pharmacopoeia 3.1.9 and other standards. Full BPOG standardized extractables test protocol (six extraction solvents, tested to four different exposure times, out to 70 days) is in process with a fully-accredited, third-party test lab.

AdvantaSil High Pressure is not intended for implantation or continuous steam applications.



Key Features

- Allows for processing at higher flow rates
- Handles short run peristaltic pump applications requiring 30 psi back pressure contact AdvantaPure Technical Support for details
- Full vacuum capabilities on most sizes
- Flexible and translucent yet durable
- Eliminates particulate shedding that can occur when cutting braid reinforced hose
- Certified free of animal-derived ingredients
- General temperature range: -65°F (-53.9°C) to 400°F (204.4°C)
- Resists temperature extremes, compression set, chemical attack, ozone, radiation, moisture and environmental exposure
- Sterilizable by autoclave or gamma irradiation
- Validated sterility assurance of 10⁻⁶ via gamma irradiation per ISO 11137 method VDmax 25 pending
- Documented lot traceable with identification on bags
- Documented quality control

Full BPOG standardized extractables test protocol in process



E

ntapure.c

w.adva

≥

AdvantaSII silicone tubing and hose products are quickly becoming recognized as superior choices for Single-Use processes worldwide. Engineers in process development and manufacturing have relied on AdvantaSil unreinforced tubing, reinforced hose, pump grade tubing and wire reinforced suction hose for years.

AdvantaSil High Pressure Unreinforced Silicone Tubing





SPECIFICATIONS

Product Number	Nominal I.D.		Wall		O.D.		Bend Radius		Standard Available
	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	Length (ft.)
APHP-0250-0375	.250	6.35	.063	1.60	.375	9.52	1	25	50
APHP-0375-0625	.375	9.52	.125	3.18	.625	15.88	1.2	30	50
APHP-0500-0750	.500	12.70	.125	3.18	.750	19.05	1.8	46	50
APHP-0750-1000	.750	19.05	.125	3.18	1.000	25.40	2.1	53	50
APHP-1000-1250	1.000	25.40	.125	3.18	1.250	31.75	5.8	147	50
Product	Burst Pressure		Recommended		Burst Pressure		Recommended		Vacuum
Number	Non-Treated		Working Pressure		Gamma Irradiated		Working Pressure		Capability
	(psi)	(psi) (bar) <u>based on 3:1</u>		45 kGy		based on 3:1		(in./Hg)	
		<u>safety factor</u> Non-Treated (psi) (bar)		(psi) (bar)		<u>safety factor</u> Gamma Irradiated			
							45 kGy		
							(psi)	(bar)	
APHP-0250-0375	125	8.6	42	2.9	144	9.9	48	3.3	>29.5
APHP-0375-0625	177	12.2	59	4.1	211	14.5	70	4.8	>29.5
APHP-0500-0750	140	9.7	47	3.2	157	10.8	52	3.6	>29.5
APHP-0750-1000	109	7.5	36	2.5	123	8.5	41	2.8	>29.5

SILIGONE

Sold by standard coil length of 50 ft. Add length suffix code "L" to product number when ordering. Example: 50 ft. of .250 in. I.D. x .375 in. O.D. tubing is product number APHP-0250-0375L.

1.8

84

26



1.9

Non-listed sizes and custom lengths are available by special order.

5.4

78

Coils are supplied double bagged in heat-sealed polybags and bulk packed.

Contact your AdvantaPure Sales Representative regarding any special product or packaging needs.

Recommended working pressures are calculated from burst testing using a 3:1 safety factor. Testing was performed at ambient temperature. Application testing is recommended.

CF = Consult factory

APHP-1000-1250

Address: NewAge Industries AdvantaPure® 145 James Way Southampton, PA 18966 U.S.A.

888-755-4370

215-526-2151

888-258-4293

215-526-2167

www.advantapure.com

sales@advantapure.com

Toll Free Phone: Phone: Toll Free Fax: Fax: Web Site: E-mail: Advanta PURE*

DISTRIBUTED BY:

5.8

28



CF

捷阀流体技术(深圳)有限公司

ً ◎ 深圳市龙岗区五和大道4012号

www.gefa-ultrapure.com.cn



©2017 NewAge® Industries, Inc. Specifications are subject to change without notice. AdvantaPure products are produced by NewAge® Industries, Inc. AdvantaSil™, NewAge Industries AdvantaPure®, Purity in Fluid Flow Systems®, NewAge®, and the "N" logo are trademarks of NewAge® Industries, Inc.





WARRANTY: NewAge Industries AdvantaPure products are warranted to be free from defects in material and workmanship. Any product found to carry such defects will be replaced without charge. This warranty is limited only to the replacement of NewAge Industries AdvantaPure products, item for item, which after examination by NewAge Industries AdvantaPure are deemed defective. NewAge Industries AdvantaPure specifically disclaims any other liability. The data supplied is provided as a helpful guideline and is believed to be reliable; however, nothing stated shall constitute a guarantee, recommendation, or warranty for any application. NOTICE: NewAge Industries, inc. has been a privately owned corporation more 1954. Neither the corporation nor ts principals are affiliated, in any way, with any other group or entity either representing themselves as or being referred to by the term NewAge.